

## 15031000 Technical Drawings

REVISION DATE







Floor Flange

NOT: The Emergency shower is mounted on the floor with 4 M10x45 hole in bolts and dowels.

Bolts and dowels will be sent with the product.


4 piece hole in anchor bolts

4 piece dowels

_	2	3	4	5	6	7	00	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25
Shower head Bowl (Ø300mm)	1" Ball Valve	1 1/4" 660 mm pipe	1 1/4" 590 mm pipe	1 1/4" 740 mm pipe	1" 500 mm pipe	1" 220 mm pipe	1/2" 85 mm pipe	Main Connection fitting	Middle connection	1" Water Outlet	Top Corner Fitting	Shower Head Fitting	Pull Rod control for shower	Emergency shower sign	Eye/face wash sign	Eye/face corner connection	Push Handle Control for Eyewash	Eyewash Bowl	Dust Cover on Eyewash Spray	Spray Nozzles	1" Valve Handle	M10x45 Hole in Bolt(4 piece)	1/2" Ball Valve for eye/face wash	1" Filter
304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	Phosphorus	Phosphorus	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	Plastic	Brass	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL	304 STAINLESS STEEL



Max using pressure: 2,8 bar Min using pressure: 1,4 bar Static test pressure: 7 bar



Screw number 1 pieces together. (1-1)

NO. DESCRIPTION

MATERIAL

- 2 Screw number 2 pieces together. (2-2)
- $\omega$ Screw number 3 pieces together. (3-3)
- Screw number 4 pieces together. (4-4)
- Screw number 5 pieces together. (5-5)

5

- <u>6</u> eyewash dish and connected completely. Spray nozzles must be to run parallel with person who see in front of shower. eyewash screwed on the middle of the Eyewash dish screwed to low and (6-6),
- 7 Please use impermeability teflon bands at pipe connection points
- 8 are on pedestal conecting part. For the connecting could use M10x45 hole in anchor bolt The shower which is finished assembly is connected pedestal by 4 holes that steel plugs.
- 9) The shower can directly connected to water network by 1" water inlet.
- 10) You can drain the waste water by connecting a suitable 1" diameter pipe or hose to the waste water outlet.

Side View

DRAWING NAME: 15031000	SHEET:  1  OF:  1	DRAWING NUMBER/DATE: 420/16-1				IST Isci Sagligi Techizati Sanayi ve Ticaret Ltd Sti İvedik OSB Mh. 2269. Cd. No.42 Yenimahalle 06374, Ankara, Türkiye www.ist.com.tr Ph 0090312 384 13 00 Fax 0090312 341 73 03	IST Isci Sagligi Tech İvedik OSB Mh. 2268 Ankara, Türkiye Ph 0090312 384 13		
Y SHOWER AND EYE/FACE WASH	RGENC	PRODUCT ISTEC TYPE ESW EMERGENCY SHOV	SIZE SCALE A4 1/100	SIZE A4		ORIGINAL EDITION  SS SS APPROXED  V FA APPROXED  V FS ST ST	FOR RFQ/DESIGN 🛭	W ====================================	FOR INFORMATION  TATUS  FOR REVIEW  FOR APPROVAL
( ) Usub o *	in the	1/00:	<b>APPROVED</b>	) XESIGNED CHECKED WPPRO	DESIGNE	DESCRIPTION	REV. DATE	7	١
(UL) (L) (ANSI	\(\frac{1}{2}\)		ST	FA	SS	FIRSTISSUE	Α		
	رن <sub>ة</sub> 				H			ľ	

Çağkan TOPCU	PREPARED
Serdar TÜRKUÇAR	APPROVED